



## Anchor, Tool, SS175 Drive Wrench with integral pins

By CHANCE Foundation Solutions  
Catalog # [C3031645](#)

SS175 Drive Tool for use with 7 5/8" (193.7 mm) bolt circle  
Kelly Bar Adapter.



### Features

- These tools include our proprietary Alignment Window that helps reduce chance of finger pinch when anchor is inserted into tool.
- These drive tools require the appropriate Kelly bar adapter, sold separately
- Each comes with bolts, nuts and lockwashers.
- Each of these drive tools includes an integral set of locking dogs that attach the drive tool to the anchor.

### Application

Anchor/Pile Installation

### General

Attachment Style	Kelly Bar Adapter
Bolt Grade	2
Coating	Painted
Drive Wrench Anchor Type	SS175 Anchor
Number of Bolt Holes	12
Torque Rating	10500 ft-lbs
Type	Anchor/Pile Installation Tools
UPC	096359570493

### Dimensions

Anchor Installation Hole Size	0.625 in
Diameter - Bolt	0.625 in
Diameter - Bolt Circle	7.625 in
Weight	31.000 lb

### Logistics

Pallet Quantity	27
Standard Package	1

### Product Assets

- [Installation Manuals - CHANCE Digital Torque Indicator](#)
- [Installation Manuals - Instructions for CHANCE Quick-Change Anchor Drive Tools](#)
- [Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide \(BR06167E\)](#)
- [Literature - SF04364E Digital Torque Indicator](#)
- [Sales Drawings - SS175 Locking Dog Drive Tool \(SA3031645\)](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - Square Shaft Anchor Drive Wrench](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

### Related Products

[C3030195](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CN-C3031645-SPEC-EN | REV 1/2024