



Low Profile Underpinning T-pipe

By CHANCE Foundation Solutions
Catalog # [PSAC1500503](#)

Low Profile Underpinning T-pipe fits SS5/SS150.



Features

- Finish: Galvanized
- Building Code Approved: Yes

Application

Helical Anchoring

General

Coating	Hot Dip Galvanized
Shaft Type	SS
Strength Rating - Ultimate	15000 lb
Type	Underpinning
UPC	096359516019

Dimensions

Weight	18.00 lb
--------	----------

Logistics

Pallet Quantity	50
-----------------	----

Product Assets

[Catalogs - CHANCE Helical Solutions Product Catalog \(CA04140E\)](#)
[Engineering Drawing - Low Profile Underpinning Bracket](#)
[ISO Certificates - Centralia_Operations_ISO_9001_2015](#)
[SDS - MSDS - Galvanized Steel Products](#)
[Video - CHANCE 4.3 Helicap 3.0 Torque Graph \(VIO4167E0420\)](#)
[Video - CHANCE 4.2 Helicap 3.0 Capacity Graph Tab \(VIO4165E0420\)](#)
[Video - Hubbell Power Systems Helical Pile Shake Table Testing \(VIO4112E\)](#)

Related Products

[PSAC1500499](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CN-PSAC1500503-SPEC-EN | REV 7/2023