



Anchor, Adapter, SS175 Threaded Stud

By CHANCE Foundation Solutions
Catalog # [T1100352](#)

SS 175 Guy Adapter with Threaded Stud.



Features

- Hot dipped galvanized per ASTM A153

Application

Helical Anchoring

General

Coating	Galvanized
EU RoHS Indicator	No
Eye Nut Style	Threaded Stud
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	100000 lb.
Type	Adapters
UPC	096359055594

Dimensions

Length	48.000 in
Weight	23.579 lb

Logistics

Pallet Quantity	30
Standard Package	1

Product Assets

- [Catalogs - CHANCE Helical Solutions Product Catalog \(CA04140E\)](#)
- [ISO Certificates - Centralia_Operations_ISO_9001_2015](#)
- [Literature - Forged Pulling Eye \(SF06013E\)](#)
- [Sales Drawings - SS175 Anchors \(SA11010018\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)

Related Products

- [Square Shaft \(SS 175\) Hardware](#)
- [Square Shaft \(SS175\) Nut Replacement](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CN-T1100352-SPEC-EN | REV 7/2023