



Wire-Ready Foundation, 10-3/4" OD x 72" Long

By CHANCE Foundation Solutions
Catalog # [T1120284](#)

Streetlight Foundation (SLF) 10.75 OD x 72" Long, 1" thick x 15" square baseplate, fixed circle, hardware included.



*Representative Image

Features

- Fixed 15" Bolt Circle
- 4 holes, 1" Dia x 3-1/2" Long
- hardware included
- Suitable for Streetlight, Roadway, and Architectural Lighting
- Other applications include EV Charging Infrastructure, 5G/6G Poles, Rail Applications, End Zone Tower Systems, Solar Array Pole Mount, and Signage

Application

Helical Anchoring

General

Base Plate Shape	Square
Bolt Hole Type	Drilled Hole
Coating	Galvanized, ASTM A-153
Ground Lug Hole	No
Hardware Packaging	Installed
Number of Bolt Holes	4
Pipe Type	Round Pipe
Type	Lighting Foundation Anchors
UPC	096359056003

Dimensions

Base Plate Dimensions	15.00 in
Base Plate Thickness	1.000 in
Bolt Length	3.50 in
Cableway Distance From Base	24 in
Cableway Length	12.00 in
Cableway Width	2.50 in
Center hole dimensions	9.25 in
Diameter - Bolt	1 in
Diameter - Bolt Circle	15 in
Foundation Diameter	10.750 in
Foundation Length	72 in
Weight	278.000 lb

Logistics

Pallet Quantity	6
Standard Package	1

Product Assets

[Case Studies - Case History - Randazzo Park \(CH04318E_1120\)](#)
[Engineering Drawing - SA1120284](#)
[Installation Manuals - Instant Foundations \(TD04365E\)](#)
[Literature - Instant Foundation Solutions \(SF04248E_0819\)](#)
[Literature - Precast Concrete Collars \(SF04273E\)](#)
[Literature - Instant Foundations and Pre-Cast Concrete Collars \(BR04331E\)](#)
[Literature - Instant Foundations® for EV Charging Stations \(SF04048E\)](#)
[Sales Drawings - SA1120284](#)
[SDS - MSDS - Galvanized Steel Products](#)
[Test Documents - Pole Load Determination Data Sheet \(TD04196E\)](#)
[Video - CHANCE Instant Foundation & Concrete Collar \(VI04163E0520\)](#)
[Video - SLF \(VI04173E1021\)](#)
[Video - CHANCE® Streetlight Foundation \(VI04147E0719\)](#)

Related Products

C3030684



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CN-T1120284-SPEC-EN | REV 1/2024

