



Pole Base Foundation, 8-5/8" OD x 84" Long

By CHANCE Foundation Solutions
Catalog # [T1120837](#)

Streetlight Foundation (SLF) 8.625 OD x 84" Long, 3/4" thick x 18" round baseplate, fixed circle, hardware included.



*Representative Image

Features

- Fixed 13" Bolt Circle
- 2 holes, 1" Dia x 2-1/2" Long
- Suitable for Streetlight, Roadway, and Architectural Lighting
- Other applications include EV Charging Infrastructure, 5G/6G Poles, Rail Applications, End Zone Tower Systems, Solar Array Pole Mount, and Signage

Application

Helical Anchoring

General

Base Plate Shape	Square
Bolt Hole Type	Tapped Bolt Hole
Coating	Galvanized
Ground Lug Hole	No
Hardware Packaging	Installed
Number of Bolt Holes	2
Pipe Type	Round Pipe
Type	Lighting Foundation Anchors
UPC	096359516316

Dimensions

Base Plate Dimensions	17.50 in
Base Plate Thickness	0.750 in
Bolt Length	2.50 in
Center hole dimensions	5.00 in
Diameter - Bolt	1 in
Diameter - Bolt Circle	13 in
Foundation Diameter	6.630 in
Foundation Length	84 in
Length	84.00 in
Weight	190.000 lb

Logistics

Pallet Quantity	9
Standard Package	1

Product Assets

- [Case Studies - Case History - Randazzo Park \(CH04318E_1120\)](#)
- [Engineering Drawing - Foundation, Airport Lighting](#)
- [Installation Manuals - Instant Foundations \(TD04365E\)](#)
- [Literature - Instant Foundation Solutions \(SF04248E_0819\)](#)
- [Literature - Precast Concrete Collars \(SF04273E\)](#)
- [Literature - Instant Foundations and Pre-Cast Concrete Collars \(BR04331E\)](#)
- [Literature - Instant Foundations® for EV Charging Stations \(SF04048E\)](#)
- [Sales Drawings - Foundation, Airport Lighting](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Test Documents - Pole Load Determination Data Sheet \(TD04196E\)](#)
- [Video - CHANCE Instant Foundation & Concrete Collar \(VIO4163E0520\)](#)
- [Video - SLF \(VIO4173E1021\)](#)
- [Video - CHANCE® Streetlight Foundation \(VIO4147E0719\)](#)

Related Products

[C3030139](#)



A proud member of the Hubbell Family.