



Pole Base Foundation for 24" High Collar, 6-5/8" OD x 109"

By CHANCE Foundation Solutions
Catalog # [T1122621](#)

Streetlight Foundation (SLF) for 24" High Collar, 6.625 OD x 109" Long.



*Representative Image

Features

- Variable mounting circle
- hardware included
- Suitable for Streetlight, Roadway, and Architectural Lighting
- Other applications include EV Charging Infrastructure, 5G/6G Poles, Rail Applications, End Zone Tower Systems, Solar Array Pole Mount, and Signage
- For use with pre-fab concrete collar

Application

Helical Anchoring

General

Coating	Galvanized
Finish Type	Galvanized
Size	6.630 in
Type	Lighting Foundation Anchors
UPC	096359766636

Dimensions

Diameter - Bolt Circle Variable	9 to 14 in
Foundation Diameter	6.630 in
Length	109.00 in

Product Assets

[Case Studies - Case History - Randazzo Park \(CH04318E_1120\)](#)
[Installation Manuals - Instant Foundations \(TD04365E\)](#)
[Literature - Instant Foundation Solutions \(SF04248E_0819\)](#)
[Literature - Precast Concrete Collars \(SF04273E\)](#)
[Literature - Instant Foundations and Pre-Cast Concrete Collars \(BR04331E\)](#)
[Literature - Instant Foundations® for EV Charging Stations \(SF04048E\)](#)
[Literature - CHANCE® PRECAST CONCRETE COLLARS \(SF04273E\)](#)
[Sales Drawings - FOUNDATION, FOR PRECAST 12 SQ BASEPLATE \(SA1122621\)](#)
[Test Documents - Pole Load Determination Data Sheet \(TD04196E\)](#)
[Video - Hubbell Power Systems Instant Foundation & Concrete Collar \(VI04163E0520\)](#)
[Video - SLF \(VI04173E1021\)](#)
[Video - Engineered Advantages of Instant Foundations \(CENT-CV-VI-EN-00424\)](#)

Related Products

[C1122610TAN](#)
[C1122610GRY](#)
[C1122610WHT](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CN-T1122621-SPEC-EN | REV 1/2024