



## Pole Base Foundation for 12" High Collar, 6-5/8" OD x 73"

By CHANCE Foundation Solutions  
Catalog # [T1122666](#)

Streetlight Foundation (SLF) for 12" High Collar, 6.625 OD x 73" Long.



\*Representative Image

### Features

- Variable mounting circle
- hardware included
- Suitable for Streetlight, Roadway, and Architectural Lighting
- Other applications include EV Charging Infrastructure, 5G/6G Poles, Rail Applications, End Zone Tower Systems, Solar Array Pole Mount, and Signage
- For use with pre-fab concrete collar

### Application

Helical Anchoring

### General

Coating	Galvanized
Finish Type	Galvanized
Size	6.630 in
Type	Lighting Foundation Anchors
UPC	096359766650

### Dimensions

Diameter - Bolt Circle Variable	9 to 14 in
Foundation Diameter	6.630 in
Length	73.00 in

### Product Assets

- Case Studies - Case History - Randazzo Park (CH04318E\_1120)
- Installation Manuals - Instant Foundations (TD04365E)
- Literature - Instant Foundation Solutions (SF04248E\_0819)
- Literature - Precast Concrete Collars (SF04273E)
- Literature - Instant Foundations and Pre-Cast Concrete Collars (BR04331E)
- Literature - Instant Foundations® for EV Charging Stations (SF04048E)
- Literature - CHANCE® PRECAST CONCRETE COLLARS (SF04273E)
- Sales Drawings - FOUNDATION, FOR PRECAST 12 SQ BASEPLATE (SA1122621)
- Test Documents - Pole Load Determination Data Sheet (TD04196E)
- Video - Hubbell Power Systems Instant Foundation & Concrete Collar (VI04163E0520)
- Video - SLF (VI04173E1021)
- Video - Engineered Advantages of Instant Foundations (CENT-CV-VI-EN-00424)

### Related Products

- [C1122611WHT](#)
- [C1122611TAN](#)
- [C1122611GRY](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CN-T1122666-SPEC-EN | REV 1/2024