


**COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES****Threaded/Set Screw Fittings: LB Assembly
2" Combo LB Assembly****C13.1**

Catalog #: COLB200

APPLICATIONS

For use with threaded rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.
N/A

PRODUCT FEATURES

Durable die cast aluminum construction
Premium powder coat finish
Includes NBR synthetic rubber gasket
Stamped aluminum cover
Combination head screw

CULUS

Listed

NEMA

NEMA 3R Rated

NEC

2014 NEC Compliant

GENERAL PRODUCT INFORMATION

Trade Size: 2"
Description Table: 2" Combo LB Assembly

PACKAGING

Package Type:	Carton
Std. Pkg.:	-
Ship Carton Qty.:	5
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	157
Ship Carton Length (in.):	16.73
Ship Carton Width (in.):	10.63
Ship Carton Height (in.):	5.71
Ctn Weight (Lbs.):	8.80
Pallet Qty:	300
UPC Number:	050169815175
I2of5:	50050169815170