

**CWM**

CONTEMPORARY LED WALL MOUNT

**DELIVERED LUMENS**

CATALOG #	LENS	LUMENS	INPUT WATTS	LPW
CWM2-30VW	FR	1591	14	112.8
CWM2-30VW	SB	1055	14	75.4
CWM2-30VW	SF	1405	14	100.4
CWM2-30VW	DIS	1344	15	94
CWM2-30VW	DISF	1336	14	93.4
CWM2-30VW	DISB	1333	14	93.2
CWM2-30VW	DIC	1010	15	70.6
CWM2-30VW	DICF	1004	14	70.2
CWM2-30VW	DICB	1011	14	70.7
CWM2-35VW	FR	1639	14	116.2
CWM2-35VW	SB	1087	14	77.6
CWM2-35VW	SF	1447	14	103.4
CWM2-35VW	DIS	1390	15	97.2
CWM2-35VW	DISF	1381	14	96.6
CWM2-35VW	DISB	1378	14	96.4
CWM2-35VW	DIC	1044	15	73
CWM2-35VW	DICF	1038	14	72.6
CWM2-35VW	DICB	1045	14	73.1
CWM2-40VW	FR	1664	14	118
CWM2-40VW	SB	1104	14	78.8
CWM2-40VW	SF	1470	14	105
CWM2-40VW	DIS	1411	15	98.7
CWM2-40VW	DISF	1403	14	98.1
CWM2-40VW	DISB	1400	14	97.9
CWM2-40VW	DIC	1061	15	74.2
CWM2-40VW	DICF	1054	14	73.7
CWM2-40VW	DICB	1062	14	74.2
CWM2-50VW	FR	1724	14	123.1
CWM2-50VW	SB	1205	14	86.1
CWM2-50VW	SF	1522	14	108.7
CWM2-50VW	DIS	1449	15	101.3
CWM2-50VW	DISF	1440	14	101.4
CWM2-50VW	DISB	1437	14	101.2
CWM2-50VW	DIC	1089	15	76.1
CWM2-50VW	DICF	1082	14	76.2
CWM2-50VW	DICB	1090	14	76.8
CWM2-30MW	FR	1924	17	113.2
CWM2-30MW	SB	1275	17	74.6
CWM2-30MW	SF	1684	17	99.1
CWM2-30MW	DIS	1810	19	94.8
CWM2-30MW	DISF	1799	19	94.2
CWM2-30MW	DISB	1794	19	93.9
CWM2-30MW	DIC	1363	19	71
CWM2-30MW	DICF	1355	19	70.6
CWM2-30MW	DICB	1351	19	70.4
CWM2-35MW	FR	1982	17	116.6
CWM2-35MW	SB	1314	17	76.8
CWM2-35MW	SF	1735	17	102

**CWM**

CONTEMPORARY LED WALL MOUNT

**DELIVERED LUMENS (CONTINUED)**

CATALOG #	LENS	LUMENS	INPUT WATTS	LPW
CWM2-35MW	DIS	1872	19	98
CWM2-35MW	DISF	1860	19	97.4
CWM2-35MW	DISB	1855	19	97.1
CWM2-35MW	DIC	1409	19	73.4
CWM2-35MW	DICF	1401	19	73
CWM2-35MW	DICB	1397	19	72.7
CWM2-40MW	FR	2013	17	118.4
CWM2-40MW	SB	1335	17	78
CWM2-40MW	SF	1761	17	103.6
CWM2-40MW	DIS	1901	19	99.5
CWM2-40MW	DISF	1889	19	98.9
CWM2-40MW	DISB	1883	19	98.6
CWM2-40MW	DIC	1431	19	74.5
CWM2-40MW	DICF	1423	19	74.1
CWM2-40MW	DICB	1418	19	73.9
CWM2-50MW	FR	2085	17	122.6
CWM2-50MW	SB	1457	17	85.2
CWM2-50MW	SF	1825	17	107.3
CWM2-50MW	DIS	1951	19	102.2
CWM2-50MW	DISF	1939	19	101.5
CWM2-50MW	DISB	1934	19	101.2
CWM2-50MW	DIC	1469	19	76.5
CWM2-50MW	DICF	1460	19	76.1
CWM2-50MW	DICB	1456	19	75.8
CWM2-30LW	FR	2332	21	111.6
CWM2-30LW	SB	1546	21	74
CWM2-30LW	SF	2059	21	98.5
CWM2-30LW	DIS	2360	25	93.3
CWM2-30LW	DISF	2346	25	92.7
CWM2-30LW	DISB	2339	25	87.1
CWM2-30LW	DIC	1774	25	69.8
CWM2-30LW	DICF	1763	25	69.4
CWM2-30LW	DICB	1758	25	69.2
CWM2-35LW	FR	2402	21	114.9
CWM2-35LW	SB	1593	21	76.2
CWM2-35LW	SF	2121	21	101.5
CWM2-35LW	DIS	2440	25	96.5
CWM2-35LW	DISF	2426	25	95.9
CWM2-35LW	DISB	2418	25	90.1
CWM2-35LW	DIC	1834	25	72.2
CWM2-35LW	DICF	1823	25	71.8
CWM2-35LW	DICB	1818	25	71.6
CWM2-40LW	FR	2439	21	116.7
CWM2-40LW	SB	1617	21	77.4
CWM2-40LW	SF	2154	21	103.1
CWM2-40LW	DIS	2478	25	97.9
CWM2-40LW	DISF	2463	25	97.4
CWM2-40LW	DISB	2456	25	97.1

**CWM**

CONTEMPORARY LED WALL MOUNT

**DELIVERED LUMENS (CONTINUED)**

CATALOG #	LENS	LUMENS	INPUT WATTS	LPW
CWM2-40LW	DIC	1863	25	73.3
CWM2-40LW	DICF	1852	25	72.9
CWM2-40LW	DICB	1846	25	72.7
CWM2-50LW	FR	2527	21	120.9
CWM2-50LW	SB	1766	21	84.5
CWM2-50LW	SF	2232	21	106.8
CWM2-50LW	DIS	2544	25	100.6
CWM2-50LW	DISF	2529	25	100
CWM2-50LW	DISB	2521	25	99.7
CWM2-50LW	DIC	1912	25	75.3
CWM2-50LW	DICF	1901	25	71.7
CWM2-50LW	DICB	1895	25	74.6
CWM2-30ML	FR	3164	30	105.5
CWM2-30ML	SB	2038	30	67.9
CWM2-30ML	SF	2723	30	91.7
CWM2-30ML	DIS	3166	37	86.7
CWM2-30ML	DISF	3180	37	87.4
CWM2-30ML	DISB	3180	37	87.1
CWM2-30ML	DIC	2387	36	65.8
CWM2-30ML	DICF	2422	36	66.5
CWM2-30ML	DICB	2409	36	66.4
CWM2-35ML	FR	3259	30	108.6
CWM2-35ML	SB	2099	30	70
CWM2-35ML	SF	2805	30	94.4
CWM2-35ML	DIS	3274	37	89.7
CWM2-35ML	DISF	3288	37	90.3
CWM2-35ML	DISB	3288	37	90.1
CWM2-35ML	DIC	2468	36	68
CWM2-35ML	DICF	2504	36	68.8
CWM2-35ML	DICB	2491	36	68.6
CWM2-40ML	FR	3310	30	110.3
CWM2-40ML	SB	2132	30	71.1
CWM2-40ML	SF	2848	30	95.9
CWM2-40ML	DIS	3324	37	91.1
CWM2-40ML	DISF	3339	37	91.7
CWM2-40ML	DISB	3339	37	91.5
CWM2-40ML	DIC	2506	36	69
CWM2-40ML	DICF	2543	36	69.9
CWM2-40ML	DICB	2529	36.3	69.7
CWM2-50ML	FR	3429	30	114.3
CWM2-50ML	SB	2327	30	77.6
CWM2-50ML	SF	2951	30	99.3
CWM2-50ML	DIS	3413	37	93.5
CWM2-50ML	DISF	3428	37	94.2
CWM2-50ML	DISB	3428	37	93.9
CWM2-50ML	DIC	2573	36	70.9
CWM2-50ML	DICF	2611	36	71.7
CWM2-50ML	DICB	2597	36.3	71.5

**CWM**

CONTEMPORARY LED WALL MOUNT

**DELIVERED LUMENS (CONTINUED)**

CATALOG #	LENS	LUMENS	INPUT WATTS	LPW
CWM4-30XW	DIS	2378	24	101.2
CWM4-30XW	DISF	2372	24	100.5
CWM4-30XW	DISB	2359	24	99.5
CWM4-30XW	DIC	1806	24	76.2
CWM4-30XW	DICF	1746	24	74
CWM4-30XW	DICB	1780	24	75.4
CWM4-35XW	DIS	2459	24	104.6
CWM4-35XW	DISF	2453	24	103.9
CWM4-35XW	DISB	2439	24	102.9
CWM4-35XW	DIC	1867	24	78.8
CWM4-35XW	DICF	1805	24	76.5
CWM4-35XW	DICB	1841	24	78
CWM4-40XW	DIS	2497	24	106.3
CWM4-40XW	DISF	2491	24	105.5
CWM4-40XW	DISB	2477	24	104.5
CWM4-40XW	DIC	1896	24	80
CWM4-40XW	DICF	1833	24	77.7
CWM4-40XW	DICB	1869	24	79.2
CWM4-50XW	DIS	2563	24	109.1
CWM4-50XW	DISF	2557	24	108.3
CWM4-50XW	DISB	2543	24	107.3
CWM4-50XW	DIC	1947	24	82.1
CWM4-50XW	DICF	1882	24	79.8
CWM4-50XW	DICB	1919	24	81.3
CWM4-30VW	DIS	3105	32	98.6
CWM4-30VW	DISF	3086	32	98
CWM4-30VW	DISB	3077	32	97.7
CWM4-30VW	DIC	2355	32	74.1
CWM4-30VW	DICF	2341	32	73.6
CWM4-30VW	DICB	2334	32	73.4
CWM4-35VW	DIS	3211	32	101.9
CWM4-35VW	DISF	3191	32	101.3
CWM4-35VW	DISB	3182	32	101
CWM4-35VW	DIC	2435	32	76.6
CWM4-35VW	DICF	2420	32	76.1
CWM4-35VW	DICB	2413	32	75.9
CWM4-40VW	DIS	3260	32	103.5
CWM4-40VW	DISF	3241	32	102.9
CWM4-40VW	DISB	3231	32	102.6
CWM4-40VW	DIC	2473	32	77.8
CWM4-40VW	DICF	2458	32	77.3
CWM4-40VW	DICB	2450	32	77.1
CWM4-50VW	DIS	3347	32	106.3
CWM4-50VW	DISF	3327	32	105.6
CWM4-50VW	DISB	3317	32	105.3
CWM4-50VW	DIC	2539	32	79.8
CWM4-50VW	DICF	2523	32	79.4
CWM4-50VW	DICB	2516	32	79.1

**CWM**

CONTEMPORARY LED WALL MOUNT

**DELIVERED LUMENS (CONTINUED)**

CATALOG #	LENS	LUMENS	INPUT WATTS	LPW
CWM4-30MW	DIS	3657	38	96.5
CWM4-30MW	DISF	3635	38	96.2
CWM4-30MW	DISB	3624	38	95.9
CWM4-30MW	DIC	2767	38	72.8
CWM4-30MW	DICF	2750	38	72.4
CWM4-30MW	DICB	2742	38	72.2
CWM4-35MW	DIS	3781	38	100
CWM4-35MW	DISF	3759	38	97.2
CWM4-35MW	DISB	3747	38	99.1
CWM4-35MW	DIC	2861	38	75.3
CWM4-35MW	DICF	2844	38	74.8
CWM4-35MW	DICB	2835	38	74.6
CWM4-40MW	DIS	3840	38	101.6
CWM4-40MW	DISF	3817	38	101
CWM4-40MW	DISB	3805	38	100.7
CWM4-40MW	DIC	2905	38	76.5
CWM4-40MW	DICF	2888	38	76
CWM4-40MW	DICB	2879	38	75.8
CWM4-50MW	DIS	3941	38	104.3
CWM4-50MW	DISF	3919	38	103.7
CWM4-50MW	DISB	3907	38	103.4
CWM4-50MW	DIC	2983	38	78.5
CWM4-50MW	DICF	2965	38	78
CWM4-50MW	DICB	2956	38	77.8
CWM4-30LW	DIS	4089	43	94.4
CWM4-30LW	DISF	4071	43	94
CWM4-30LW	DISB	4069	43	93.8
CWM4-30LW	DIC	3102	43	71.6
CWM4-30LW	DICF	3126	43	72.2
CWM4-30LW	DICB	3017	43	69.7
CWM4-35LW	DIS	4228	43	97.6
CWM4-35LW	DISF	4209	43	97.2
CWM4-35LW	DISB	4207	43	96.9
CWM4-35LW	DIC	3207	43	74.1
CWM4-35LW	DICF	3232	43	74.6
CWM4-35LW	DICB	3120	43	72
CWM4-40LW	DIS	4293	43	99.2
CWM4-40LW	DISF	4275	43	98.7
CWM4-40LW	DISB	4272	43	98.4
CWM4-40LW	DIC	3257	43	75.2
CWM4-40LW	DICF	3282	43	75.8
CWM4-40LW	DICB	3168	43	73.2
CWM4-50LW	DIS	4408	43	101.8
CWM4-50LW	DISF	4389	43	101.4
CWM4-50LW	DISB	4386	43	101.1
CWM4-50LW	DIC	3344	43	77.2
CWM4-50LW	DICF	3370	43	77.8
CWM4-50LW	DICB	3252	43.3	75.1