

# CU2SO

SEALED OPTIC LED EMERGENCY LIGHT

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

## FEATURES

- LED Life-cycle of more than 10 years
- Quick Installation
- Dual-Voltage 120/277VAC Input
- Includes long-life Nickel Cadmium battery for UL recognized 90 minute emergency lighting
- Wet Location Listed 0°C to 40°C (32°F to 104°F)
- Fully Adjustable lamp-heads
- Includes test switch and AC-On indicator



## SPECIFICATIONS

### DESCRIPTION

- The CU2SO provides 90 minutes of emergency lighting in the event of power outage
- The CU2SO offers quality and value with a compact and attractive LED based emergency light
- The white housing is made of high impact UL flame rated thermoplastic, and clear cover is made of impact resistant polycarbonate

- The fully gasketed and shielded housing protects the unit from wind driven rain
- Snap together design for quick and easy installation with option of wall or ceiling mount

### APPLICATION

- The CU2SO can be applied in areas susceptible to rain and severe moisture
- Some of these include outside over doors, in parking garages, around pools or in basements.

tradeSELECT®



### RELATED PRODUCTS

Ø [CU2FO - Fixed Optic LED Emergency Light](#)

### COMPLIANCES

- UL924 Listed for Wet Location
- NFPA 101
- NFPA 70
- OSHA

### WARRANTY

- 2 year full unit warranty
- See [HLI Standard Warranty](#) for additional information

## ORDERING GUIDE

Catalog Number	Description
CU2SO	Clear poly-carbonate shield with white thermoplastic housing, Dual LED lamps, UL Wet Location Listed, 120/277VAC Input, 3.6VDC, 136W per lamp-head, 99 lumens per head

## ENERGY CONSUMPTION DIMENSIONS

	120 VAC	277 VAC
CU2SO	3.59W	3.40W

Single Carton Weight	3 lbs.
Master Carton Quantity	12 each

