



DATE:	LOCATION:
	1
TYPE:	PROJECT:
CATALOG #:	

tradeSELECT^{*}



RELATED PRODUCTS

8 CU2W - Wet Location LED Emergency Unit

FEATURES

- The CWR remote lamps are driven exclusively by the Compass CU2W with remote capacity
- Quick installation
- UL924 listed for 10°C to 40°C (50°F to 104°F)

SPECIFICATIONS

DESCRIPTION

- The CWR single and double remote heads offer quality and value with a compact and attractive LED based outdoor remote emergency light
- Includes mounting base and lampheads in durable die-cast construction. Lampheads are fully gasketed, fully adjustable and glare-free for operation in outdoor and wet environments
- The CWR remote lamps are driven exclusively by the Compass CU2W with remote capacity.

APPLICATION

 The CWR remote heads can be applied over path of egress doors in areas affected by rain, moisture and condensation

APPLICATION

• UL924

WARRANTY

- 2 year full unit warranty
- See <u>HLI Standard Warranty</u> for additional information


ORDERING GUIDE

Catalog Number	Description	Voltage	Lamp Watts (Each)
CWRS	Single-head LED Remote CU2W Only, Grey Finish	9.6Vdc	1.0W
CWRD	Double-head LED Remote for CU2W Only, Grey Finish	9.6Vdc	1.0W




CU2W Emergency Light

DIMENSIONS



Single Carton Weight (single)	2 lbs.
Single Carton Weight (double)	2 lbs.
Master Carton Quantity	12 each

CWRS 2.6"



Note

Photometric files available for download at www.compasslightingproducts.com Outlet box must have a minimum depth of 3" (Not Included)

utiet box mast nave a minimum depth of 5 (Not include)

