



## 15 kV, 110 kV BIL, Type C Standard Polymer Cutout w/300A Solid Blade

by CHANCE Utility  
Catalog ID: CP710133L

15 kV, 110 kV BIL, Standard Type C Polymer Cutout with a 300A solid blade, large eye-bolt connector and no bracket.

\* Representative image

## Product Details

### General

Bracket Type	No Bracket
Description - Replacement Fuse Holder	T710-133T
Type	Cutout
UPC	096359368908

### Dimensions

Weight	11.201 lb
--------	-----------

### Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

### Logistics

Pallet Quantity	63 EA
Standard Package	1

For further technical assistance, please contact us

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)