



15 kV, 110 kV BIL, Type C Standard Polymer Cutout w/200A 12kAIC fuseholder

by CHANCE Utility
Catalog ID: CP710143E

15 kV, 110 kV BIL, Standard Type C Polymer Cutout with a 200A, 12kAIC fuseholder, small eyebolt connector and no bracket.

* Representative image

Product Details

General

Bracket Type	No Bracket
Description - Replacement Fuse Holder	T710-143T
Type	Cutout
UPC	096359450504

Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	200 A
Fuselink Current Range	140A to 200A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

Logistics

Pallet Quantity	63 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service
 Hubbell Power Systems
 210 N. Allen Centralia, MO 65240 USA
 Phone: (573) 682-5521
 Fax: (573) 682-8475
 Email: hpscsc@hubbell.com

International Customer Service
 Phone: +1-573-682-5521
 Fax: +1-573-682-8516
 Email: hpsintlcs@hubbell.com