



# 15/27 kV, 125 kV BIL, Type C Loadbreak Polymer Cutout w/100A 8kAIC fuseholder

by CHANCE Utility  
Catalog ID: CP730211L

15/27 kV, 125 kV BIL, Loadbreak Type C Polymer Cutout with a 100A, 8kAIC fuseholder, large eyebolt connector and no bracket.



\* Representative image

## Product Details

### General

Bracket Type	No Bracket
Description - Replacement Fuse Holder	T730-211T
Type	Cutout
UPC	096359452164

### Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	17.1" (434mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	No Restrictions thru 14.9kV; *20.8 thru 24.9kV
Temperature Rise - Max. at 300A	40° C
Voltage - Radio Interference	36.2 micro-volts @ 15.66kV
Voltage Rating	15/27 kV

### Logistics

Standard Package	1
------------------	---

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscscs@hubbell.com](mailto:hpscscs@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)