



## CTDD424212

by Wiegmann  
Catalog ID: CTDD424212

N3R CT Double Door Hinged-Cover 42X42X12 Carbon Steel - Gray

- Manufactured from 12 gauge carbon steel. Fully seam welded and ground smooth, with weep hole. Drip shield. Lift off hinges, gasketed doors. Supplied with non-locking "T" handle. Meter seal provisions. Mounting holes in back. Supplied with studs in back of enclosure to support optional wood sub panel.

## Product Details

### General

|                         |  |
|-------------------------|--|
| Application             | Enclosures are designed as a housing for current and voltage transformers, recorders, meters, junction, service box, relay, and/or for terminal instrumentation. |
| Color                   | Gray   |
| Construction            | Seam and Tack Welded   |
| Cover Type              | Hinged Cover   |
| Finish Type             | Textured   |
| Knockouts               | No   |
| Listings                | UL, CSA  |
| Material                | Carbon Steel   |
| Mounting Method         | Mounting Holes   |
| Number of Doors (Fixed) | 2  |
| Type                    | Enclosure  |
| UPC                     | 786725854028   |

### Dimensions

|                |             |
|----------------|-------------|
| Cubic Capacity | 21168 cu.in |
| Depth          | 12 in       |
| Height         | 42 in       |
| Weight         | 174 lb      |
| Width          | 42 in       |

### Certifications and Compliance

|                  |  |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul> |
| Nema Rating      | 3R   |
| UL Listed        | Yes  |