



D350-4I

by CMC
Catalog ID: D350-4I

Space-Saver Secondary Connectors, Dual-Rated for Aluminum or Copper Conductors

- Clear plated for low-contact resistance.
- Fully tested to ANSI C119.4 for Class 'A' connectors.
- Supplied with radial-tipped set-screws.
- 105°C Rated black plastisol cover available.
- Includes CO-OX oxide inhibitor in all conductor holes.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of a 9" insulated Allen wrench.

Product Details

General

Material	Aluminum
Type	D/DO
UPC	192663073771

Dimensions

Dimensions	2.11 in x 1 in x 2.5 in
Height	2.5 in
Length	2.11 in
Width	1 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	350 Kcmil - #12 AWG
Number Of Conductors	4



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

