

**Distribution Arresters NLZ-P 15 kV**

By Delmar  
Catalog # [NLZP-1510](#)

The polymer distribution arresters model NLZ-P are designed to protect equipment against surges in distribution lines. Manufactured with metal oxide varistors without series gaps and UV resistant silicone rubber housing. Arresters are supplied with automatic ground lead disconnecter. Assembled and tested in accordance to ABNT / ANSI / IEC standards.

**Features**

- Available in the rating of 3 kV to 36kV - 10kA
- Hot dip galvanized NEMA bracket
- Polymer insulating bracket
- Line and ground terminals for 10 to 2/0AWG cables
- High relief identification on the housing

**General**

Catalog Number	NLZP-1510
Residual Voltage (1 ? (max.))	54.30
Residual Voltage (8 x 20? (max.))	50.00

**Dimensions**



\*Representative Image

Height	310 mm
Length	100 mm

**Electrical Ratings**

Creep and Leakage Distance	560 mm
Operating Voltage	12700 VAC
Voltage Rating	15 kV

**Product Assets**

- [Catalogs - Para-raios de Distribuição NLZ-P 3kV a 36kV](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)
- [Specifications - NLZP-1510](#)