

## Distribution Arresters NLZ-P 36 kV

By Delmar

Catalog # [NLZP-3610](#)

The polymer distribution arresters model NLZ-P are designed to protect equipment against surges in distribution lines. Manufactured with metal oxide varistors without series gaps and UV resistant silicone rubber housing. Arresters are supplied with automatic ground lead disconnecter. Assembled and tested in accordance to ABNT / ANSI / IEC standards.

### Features

- Available in the rating of 3 kV to 36kV - 10kA
- Hot dip galvanized NEMA bracket
- Polymer insulating bracket
- Line and ground terminals for 10 to 2/0AWG cables
- High relief identification on the housing

### General

Catalog Number	NLZP-3610
Residual Voltage (1 ? (max.))	129.40
Residual Voltage (8 x 20? (max.))	110.00



\*Representative Image

### Dimensions

Height	415 mm
Length	140 mm

### Electrical Ratings

Creep and Leakage Distance	1000 mm
Operating Voltage	29000 VAC
Voltage Rating	36 kV

### Product Assets

[Catalogs - Para-raios de Distribuição NLZ-P 3kV a 36kV](#)  
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)  
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)