

SDV-100 Arrester 1010 C

By Delmar
Catalog # [SDV 1010-C](#)

SDV-100 Arrester 1010 C



Features

- TYPE L BRACKET

Application

Distribution

General

Bracket Type	L
Cantilever Bending Strength - Max.	59.008 lb.
Color	Gray Housing
Color - Insulator	Gray
Insulator Type	POLYMER HOUSING

Dimensions

Dimensions	240 mm x 180 mm x 150 mm
Height	150 mm
Length	240 mm
Weight	2.5 kg
Width	180 mm

Electrical Ratings

Arc Distance - Dry	210mm
BIL	95 kV
Creep and Leakage Distance	470mm
Current - Low Current Long Duration (LCLD) Test	250 A

Certifications and Compliance

Industry Standard(s)	ABNT / IEC
----------------------	------------