

SDV-100 Arrester 0310 CPT

By Delmar  
Catalog # [SDV 0310-CPT](#)



SDV-100 Arrester 0310 CPT

Features

TYPE L BRACKET / WILDLIFE PROTECTION / GROUNDING STRAP

Application

Distribution

General

|                                    |                 |
|------------------------------------|-----------------|
| Bracket Type                       | L               |
| Cantilever Bending Strength - Max. | 59.008 lb.      |
| Catalog Number                     | SDV 0310-CPT    |
| Color                              | Gray Housing    |
| Color - Insulator                  | Gray            |
| Insulator Type                     | POLYMER HOUSING |

Dimensions

|            |                          |
|------------|--------------------------|
| Dimensions | 240 mm x 180 mm x 150 mm |
|------------|--------------------------|

|        |        |
|--------|--------|
| Height | 150 mm |
| Length | 240 mm |
| Weight | 2.5 kg |
| Width  | 180 mm |

Electrical Ratings

|                            |       |
|----------------------------|-------|
| Arc Distance - Dry         | 210mm |
| BIL                        | 95 kV |
| Creep and Leakage Distance | 470mm |
| Current - Low Current Long | 250 A |
| Duration (LCLD) Test       |       |

Certifications And Compliance

|                      |            |
|----------------------|------------|
| Industry Standard(s) | ABNT / IEC |
|----------------------|------------|

Product Assets

[Catalogs - Para-raios de Distribuição SDV 100 3kV a 36kV](#)  
[Specifications - SDV 0310-CPT](#)