

SDV-100 Arrester 2410 C

By Delmar
Catalog # [SDV 2410-C](#)

SDV-100 Arrester 2410 C



Features

TYPE L BRACKET

General

Application	Distribution
Bracket Type	L
Cantilever Bending Strength - Max.	59.008 lb.
Color	Gray Housing
Color - Insulator	Gray
Insulator Type	POLYMER HOUSING

Dimensions

Dimensions	335 mm x 220 mm x 245 mm
Height	245 mm
Length	335 mm
Weight	3.4 kg
Width	220 mm

Electrical Ratings

Arc Distance - Dry	305mm
BIL	150 kV
Creep and Leakage Distance	725mm
Current - Low Current Long	250 A
Duration (LCLD) Test	

Certifications And Compliance

Industry Standard(s)	ABNT / IEC
----------------------	------------

Product Assets

[Catalogs - Para-raios de Distribuição SDV 100 3kV a 36kV](#)