

SDV-100 Arrester 3310 C

By Delmar
Catalog # [SDV 3310-C](#)

SDV-100 Arrester 3310 C



Features

TYPE L BRACKET

General

Application	Distribution
Bracket Type	L
Cantilever Bending Strength - Max.	59.008 lb.
Color	Gray Housing
Color - Insulator	Gray
Insulator Type	POLYMER HOUSING

Dimensions

Dimensions	420 mm x 220 mm x 330 mm
Height	330 mm
Length	420 mm
Weight	3.6 kg
Width	220 mm

Electrical Ratings

Arc Distance - Dry	385MM
BIL	200 kV
Creep and Leakage Distance	1000mm
Current - Low Current Long	250 A
Duration (LCLD) Test	

Certifications And Compliance

Industry Standard(s)	ABNT / IEC
----------------------	------------

Product Assets

[Catalogs - Para-raios de Distribuição SDV 100 3kV a 36kV](#)