



Medium Duty Fiberglass Deadend Arm, 36"

by CHANCE Utility
Catalog ID: DEM36SPEB

Deadend Arm, 2-1/2" x 36" Medium Duty Fiberglass. Base and end fittings are aluminum alloy w/ eye bolts.



Product Details

General

Duty	Medium Duty
Material	Fiberglass
Strength Rating - Minimum Ultimate, Longitudinal (L)	7,500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	6,000 lb
Type	Fiberglass Deadend Arm
UPC	096359230984

Dimensions

Diameter - Rod / Tube	2.5 in
Length	36.00 in
Mounting Bolt Spacing	10.00 in
Weight	18.7 lb

Logistics

Carton Quantity	2 EA
Pallet Quantity	24 EA
Standard Package	2

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com