



# Medium Duty Fiberglass Deadend Arm, 54"

by CHANCE Utility  
Catalog ID: DEM54DP

Deadend Arm, 2-1/2" x 54" Medium Duty Fiberglass. Base and end fittings are aluminum alloy.



\* Representative image

## Product Details

### General

Duty	Medium Duty
Material	Fiberglass
Strength Rating - Minimum Ultimate, Longitudinal (L)	4,300 lb
Strength Rating - Minimum Ultimate, Vertical (V)	3,400 lb
Type	Fiberglass Deadend Arm
UPC	096359233886

### Dimensions

Diameter - Rod / Tube	2.5 in
Length	54.00 in
Mounting Bolt Spacing	10.00 in
Weight	26.1 lb

### Logistics

Pallet Quantity	24 EA
Standard Package	2

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)