



Medium Duty Fiberglass Deadend Arm, 54" (No Eye Bolts)

by CHANCE Utility
Catalog ID: DEM54SP

Deadend Arm, 2-1/2" x 54" Medium Duty Fiberglass. Base and end fittings are aluminum alloy, no eye bolts.



* Representative image

Product Details

General

Duty	Medium Duty
Material	Fiberglass
Strength Rating - Minimum Ultimate, Longitudinal (L)	4,300 lb
Strength Rating - Minimum Ultimate, Vertical (V)	3,440 lb
Type	Fiberglass Deadend Arm
UPC	096359239307

Dimensions

Diameter - Rod / Tube	2.5 in
Length	54.00 in
Mounting Bolt Spacing	10.00 in
Weight	24.8 lb

Logistics

Pallet Quantity	24 EA
Standard Package	2

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com