



DESS750-6

by CMC
Catalog ID: DESS750-6

Rubber Insulated Secondary Connectors, Dual rated connectors for Aluminum or Copper conductors, CO-OX oxide inhibitor is omitted

- Plug Interlock Mechanism for Dead-Front construction. Switch cannot be turned “ON” without fully inserted plug. Plug cannot be removed with switch in “ON” position
- Ground Fault Options Available
- Spacious wiring room that meets NEC wire bending requirements.
- Adjustable mounting lugs
- Quick Release Cover Bolts with Triple Leads for faster removal
- Electrostatically applied polyester/epoxy finish
- Breaker Handle has provisions for locking “ON” or “OFF” with up to three Padlocks

Product Details

General

Material	Aluminum Alloy, 6061-T6
Receptacle Type	Mechanically Interlocked
Series	VBQ
Type	Pin & Sleeve
UPC	781810669945 783936019390

Dimensions

Height	3.065 in
Length	9.25 in
Width	8.15 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Number Of Conductors	6
Number Of Wires	3

Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2, Groups B, C, D• Class I, Zone 2, Groups IIB+H2, IIA• Class II, Divisions 1 & 2, Groups F, G• Class III, Divisions 1 & 2
Nema Rating	3, 7(C, D), 9(F, G)

Logistics

Carton Quantity	1
-----------------	---



CONNECTOR MANUFACTURING COMPANY

3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

