



* Representative image

BOLT, THIMBLEYE, STRAIGHT, 5/8in x 18in

by CHANCE Utility
Catalog ID: DG1F18

Straight thimbleye bolt, 5/8" diameter x 18" length, with 6" thread length and cone pointed end. Includes one square nut. Internal eye dimensions are 9/16" x 11/16". Rated tensile strength is 12,400 lbs. Hot dip galvanized per ASTM A-153. RUS listed, ao - Bolt, strand eye, straight (thimble eye).

Product Details

General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb
Type	Thimbleye Bolts
UPC	096359369813

Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Distance From Pole	N/A
Length	18.00 in
Length - Threaded Area	6
Weight	1.96 lb

Logistics

Pallet Quantity	800 EA
-----------------	--------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com