



# BOLT, THIMBLEYE, ANGLE, 5/8in x 8in

by CHANCE Utility  
Catalog ID: DG4F8

Angled thimbleye bolt, 5/8" diameter x 8" length, with 4" thread length and cone pointed end. Includes one square nut. Internal eye dimensions are 9/16" x 11/16". Rated tensile strength is 12,400 lbs. Hot dip galvanized per ASTM A-153. RUS listed, ao - Bolt, strand eye, straight (thimble eye).



\* Representative image

## Product Details

### General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb
Type	Thimbleye Bolts
UPC	096359369905

### Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Distance From Pole	N/A
Length	8.00 in
Length - Threaded Area	4
Weight	1.22 lb

### Certifications and Compliance

Industry Standard(s)	ANSI C135.5
----------------------	-------------

### Logistics

Pallet Quantity	2000 EA
-----------------	---------

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)