

DQ8-250I

by CMC

Catalog ID: DQ8-250I

Space-saver stud-mount transformer connectors

- Clear plated for low-contact resistance
- Fully tested to ANSI C1194 for Class 'A' connectors
- Offers fast, economical, reusable, and dependable connections
- Supplied with aluminum radial-tipped set-screws
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole
- Each unit individually wrapped and labeled for ease of identification and cleanliness
- For installation, CMC® recommends the use of a 9" insulated Allen wrench
- A torque wrench should be used to ensure the proper torque is achieved



Product Details

Dimensions

Height	2 in
Length	5 in
Width	1 in

Conductor Related

Number Of Conductors	8
----------------------	---