



* Representative image

Stud Connector, Bronze

by ANDERSON
Catalog ID: DS1420012

Stud Connector, Bronze, 1-1/2-12 Stud to 0.46-1.632 Cable or 3/8 - 1-1/4 IPS Tube. STUD, BRZ 1-1/2-12, .460-1.632 IN

Product Details

General

Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug Holes	0
Number of Stud Threads	12
Type	Stud to Tube or Cable
UPC	096359300311

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Diameter - Stud	1.5 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	8.918 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

Conductor Related

Conductor Diameter - Maximum	1.632 in
Conductor Diameter - Minimum	0.46 in
Conductor Diameter Range	0.46 - 1.632
Conductor Type	Copper

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com