



\* Representative image

## DTHB0634S

by Acme Electric  
Catalog ID: DTHB0634S

Prop65\_Cancer&Reproductive

Drive Isolation Transformer - Three Phase, 575Δ - 460Y/266V, 63kVA

- Copper terminations for trouble free operation
- Wound core and strip winding for low losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units
- Optional weather shield - WSA2

### Product Details

#### General

ANFC Taps	2
BNFC Taps	2
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	575Δ
Product Category	Drive Isolation Transformer
Secondary Voltage	460Y/266 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503001035
Winding Material	AL
kVA	63

#### Dimensions

Height	29.9 in
Length	22.37 in
Weight	550 lb
Width	28.15 in

#### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	575D V

#### Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 2
UL Standard	UL 1561