



\* Representative image

## DTHB72S

by Acme Electric  
Catalog ID: DTHB72S

Prop65\_Cancer&Reproductive

Drive Isolation Transformer - Three Phase, 575Δ - 460Y/266V, 7.5kVA

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

## Product Details

### General

ANFC Taps	1
BNFC Taps	1
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	575Δ
Product Category	Drive Isolation Transformer
Secondary Voltage	460Y/266 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	004750369585
Winding Material	CU
kVA	7.5

### Dimensions

Height	15.21 in
Length	7.37 in
Weight	180 lb
Width	19.25 in

## Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	575D V

## Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506