



* Representative image

Anchor, PISA 6, 2-10in, 1in threads

by CHANCE Utility
Catalog ID: E1020823

Pisa 6 Anchor Helix- 6,000 Ft Lbs (8,136 N-M), Two 10" (254 mm) Helices for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.

- Installed with Chance anchor wrench C3031064 or C3030983
- Anchor has curvilinear leading edges to help penetrate rocky soils and to reduce damage during installation
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint

Product Details

General

Coating	Painted
Number of Helices	2
Torque Rating	6000 ft-lbs
Type	Anchor Helix
UPC	096359233282

Dimensions

Anchor Helix Diameter(s)	10 in - 10 in
Anchor Hub Size	1.500 in
Rod Diameter	• 0.750 • 1.000 in
Weight	34.496 lb

Logistics

Pallet Quantity	30 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com