

HUBBELL

Power Systems

Bushing Braze/Crimp Style Draw Lead Terminal

By Electro Composites
Catalog # [S-5085-5782](#)



1 1/4-12 to 0.625" ID Braze/Crimp Style Draw Lead Terminal (115kV & Above) 800A Max current - For use with Electro Composites SDC Style Bushings and PCORE PRC & POC Style Bushings

*Representative Image

Features

- Draw Lead Terminal
- 115kV and above
- 800A Max Current
- Fabricated with electrolytic copper
- For use with Electro Composites and PCORE HV IEEE Bushings

General

Application	Condenser Bushings
Material	Electrolytic Copper
Thread Size - Female	0.625" ID
Thread Size - Male	1 1/4-12
Type	Drawlead Connector

Dimensions

Diameter - Outside	1.25 in
Height	1.25 in
Length	5.38 in

Electrical Ratings

Current Rating	800 A
kV Class	115 kV - 500 kV

Certifications And Compliance

Industry Standard(s)	IEEE
----------------------	------

Product Assets

[Sales Drawings - S-5085-5782](#)