



Bronze Vise Connector with Shear Head

By EMC
Catalog # [EM-2379SH](#)



Accommodates #1/0-#4/0 AWG str., 390"-.552" (9.93-14.05mm), Torque shear head

Features

- "Tongue and Groove" alignment channels with non-removable torque shear head bolt

Conductor Related

Conductor Size #1/0-#4/0 AWG str.

Product Assets

[Video - Hubbell Power Systems Vice Type Clamp \(VI0593E\)](#)

[Video - Hubbell Power Systems Bolted Parallel Groove, Vise Type, and U Bolt Clamps \(VI05052E1019\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
EMC-EM-2379SH-SPEC-EN | REV 1/2024