



Offset Side Open Deadend

By EMC
Catalog # [EM-SODE20397OS-SRP](#)

Conductor Range Min 2/0 AAC, AAAC, ACSR, 2/0 Cu - Max
Conductor Range 397.5 AAC, AAAC, ACSR 397.5 Cu

Features

Single jaw design for easy installation, does not require wrenches or special tooling

General

Catalog Number EM-SODE20397OS-SRP

Dimensions

Dimensions	11.25 in x 4.35 in x 4.35 in
Height	4.35 in
Length	11.25 in
Weight	3.785 lb
Width	4.35 in

Product Assets

- [Catalogs - Bonding, Grounding, and Locating Solutions](#)
- [Sales Drawings - EM-SODE20397OS-SRP-CC](#)
- [Specifications - EM-SODE20397OS-SRP](#)