



# 12x10x4 Low Profile Polycarbonate Enclosure with Solid Door, Latch Lock, Cord Grip and Back Plate **ATS-03852** **(ATS-12104-LP-S-L-CG-BBP)**



Series of low-profile polycarbonate enclosure featuring shallow depths

## Features

- Low profile design for applications requiring shallow depth enclosures
- Blank back plate
- Solid door, latch lock and integrated padlock hasp, cord grip

## Benefits

- Protects valuable network equipment from environmental threats and tampering
- NEMA rated protection
- Indoor or outdoor applications

## Mechanical Specifications

- Dimensions : 12" x 10" x 4" (304.8 x 254 x 101.6mm)
- Weight: 5 lbs. (2.27 kg.)
- Material: Polycarbonate
- Color: Gray
- Door Type: Solid
- Lock Type: Latch with integrated pad lockable hasp
- Cord Grip: Yes
- Equipment Installation: Blank Back plate
- Enclosure Installation: Integrated Wall Flange
- NEMA Rating: 4X

**Environmental Specifications** Installation  
Environment: Indoor or Outdoor

**Warranty**  
2 Year Limited

©2025 AccelTex Solutions. All rights reserved.

Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Incorporated. All other trademarks are the property of their respective owners. Responsibility for the use and application of AccelTex Solutions materials rests with the end user.

[www.hubbell.com/acceltex](http://www.hubbell.com/acceltex)

FILE-NAME: EP-ACC-SPEC-EN-03616 | 07/2025



A Hubbell brand