

Custom Fiber Trunk Assemblies

FIBERHUBB™

Let Hubbell Be Your Fiber Connection

Hubbell's flexible modular cabling system provides the customization and bandwidth you need for today's high-performance networks. FIBERHUBB™ MPO assemblies future-proof your network with less cabling and lower installation costs than legacy infrastructure.

FiberHubb trunk assemblies mate with all Hubbell cassettes and adapter panels to complete the end-to-end fiber solution. Save time and labor with assemblies designed to easily migrate to 40G, 100G, 200G, and beyond - no new cords or recabling!

Hubbell's dedicated fiber optic facility is 100% tested and inspected to the industry's highest quality standards. Our quick turn ordering program supports specialized projects, application changes, and high-volume demand.


Features

- Customizable connectors, length, color, and cable construction
- Built with Corning ClearCurve® fiber
- Premium low-loss connector options provide easy polarity and gender field changes
- Available in all standard fiber counts
- Assembled in USA

Standards

- GR-326; Telcordia
- ANSI/TIA-568.3-D
- IEEE 802.3
- RoHS; UL 94 V-0; NFPA 262

ClearCurve is a registered trademark of Corning Incorporated.




IEEE MPO Transceiver Lane Assignments

Multimode

- 40GBASE-SR4
- 100GBASE-SR4
- 200GBASE-SR4
- 400GBASE-SR4

Singlemode

- 40GBASE-LR4
- 100GBASE-LR4
- 200GBASE-LR4
- 400GBASE-LR4



*Above standards depict scalable 4 channel pathways only. To learn more about IEEE standards and lane assignments please see the Hubbell catalog or reach out to a local Hubbell representative for more information.

MPO Low Loss Performance

Parameter	Single Mode (OS2)	Multimode (OM4)
Insertion Loss (Typ)	0.1	0.08
Insertion Loss (Max)	0.3	0.3
Return Loss	≥ 60	≥ 25
Max Attenuation (dB/km)	0.5 / 0.4	3.0 / 1.0
Link Length (m)	10,000 (10Gb)	550 (10Gb)
Operating Temp (°C)	-40 to +75	

Physical Specifications

Fiber Count	Nominal OD in (mm)	Weight lbs/km	Bend Radius (cm)		Temperature Range	
			Operation	Install	Storage	Operating
12	0.12 (3)	12.5	2	4	-40C to 70C	0C to 70C
24	0.25 (6.3)	87.5	6.3	12.6	-40C to 70C	0C to 70C
48	0.26 (6.6)	100	6.6	13.2	-40C to 70C	0C to 70C
72	0.31 (8)	150	8	16	-40C to 70C	0C to 70C
96	0.37 (9.3)	200	9.3	18.6	-40C to 70C	0C to 70C
144	0.42 (10.6)	250	10.6	21.2	-40C to 70C	0C to 70C

Catalog Number Configurator

Fiber Count	Cat #	Fiber Type	Cat #	Jacket Color	Cat #	End A	Cat #	End B	Cat #	Polarity	Cat #	Labeling	Cat #	Length	Cat #	Pulling Eye	Cat #
12	12	OM4	M4	Aqua (OM4)	AQ	MPO	MPO	MPO	MPO	Type A	A	Custom label	CL	Feet	1-1999	Yes	PE
24	24	OS2	SM	Yellow (OS2)	YW	LC	LC	LC	LC	Type B	B					No	NPE
48	48			Any	XX			Open	X	Type C	C						
72	72																
96	96																
144	144																

Example part: **FPC-LTP12M4AQ-MPO-MPO-A-10FT-NPE**

Fiber cord, plenum, 12F, OM4, MPO to MPO, Type A, 10 Feet, No pulling eye

(Assumes FPC-LTP for loose tube plenum cable construction)

*Above configuration table represents common builds. Custom fiber counts, cable construction, and jacket colors available upon request. Contact a Hubbell representative for more information.

Total FiberHUBB® Solution



Duplex patch cord

MPO cassette

Custom MPO trunk

MPO cassette

Duplex patch cord



A proud member of the Hubbell family.

©2023 Hubbell Premise Wiring. All rights reserved. Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Incorporated. All other trademarks are the property of their respective owners. hubbell.com/hubbellpremisewiring

Phone 1-800-626-0005 | Fax 1-860-535-8328

EP-PREM-TECH-SF-EN-01122 | REV 08 2023