



Catalog # 232D

# 4 IN. SQUARE BOX, DRAWN, 2-1/8 IN. DEEP

TEN 1/2 IN. AND SIX 3/4 IN. KO'S

## FEATURES

- Ideal for exposed work applications
- Recessed screw heads allow quick installation
- Drawn construction
- Ten 1/2 In. and six 3/4 in. knockouts
- 30.3 Cu. In. capacity
- Threaded ground bump

## APPLICATIONS

- Designed to enclose electrical wiring, switches, receptacles or lighting fixtures
- Constructed from 1/16 In. pre-galvanized steel
- #8-32 cover mounting screws included



## CERTIFICATIONS



## SPECIFICATIONS

UPC NUMBER:	050169995013
EA LENGTH/DEPTH (IN.):	2.13
EA WIDTH (IN.):	4.00
EA HEIGHT (IN.):	4.00
WT. EA. (LBS.):	0.593
PRODUCT UPC-A LABELED:	NO

## PACKAGING

CASE 12OF5:	50050169995018
STANDARD CARTON QTY:	25
MIN ORDER QTY:	25

