


RaynGuard® 2-Gang Weatherproof In-Use Cover

Catalog #: MX6200



55-in-1
Configurations

Feature Benefit

- Provides 3-1/2 inches of depth inside while in use

Product Features

- Heavy duty die-cast aluminum construction
- Patented QuickFit keyhole mounting system allows installation in under a minute
- Includes attached gasket and mounting hardware
- Pre-configured for GFCI with patented Knockout technology for alternate devices
- Lockable tab (fits up to 1/4 in. shackle)
- Premium Powder Coat

Applications

- Designed for use whenever weatherproof protection is required while an outlet is in use

Certifications



NEMA 3R Rated
NEC - Extra Duty Rated

Product Specifications

UPC Number:	092326104838
Ea Length/Depth (in.):	3.48
Ea Width (in.):	5.12
Ea Height (in.):	6.12
Wt. Ea. (Lbs.):	0.972
Color:	Gray
Gangs:	2
Package Type:	Shrink
Package Contents:	1
Product UPC-A Labeled:	Yes

Shipping

I2of5:	40092326104836
Standard Carton Qty:	4
Min Order Qty:	1
Ship Carton Length (in.):	14.76
Ship Carton Width (in.):	5.31
Ship Carton Height (in.):	6.69
Ship Carton Weight (Lbs.):	3.886
Pallet Qty:	504



A proud member of the Hubbell family.

©2024 TayMac. All rights reserved.
Hubbell, TayMac and the Hubbell and TayMac logos are registered trademarks of Hubbell Incorporated. All other trademarks are the property of their respective owners.
www.hubbell.com/taymac | 800-526-5416