

FF1010159CFM115VB

by Wiegmann
Catalog ID: FF1010159CFM115VB

NEMA 12 Filter Fan 115 Volt 159 Cubic Feet Per Minute 9.8X9.8 -Black

The latest passive technology for fan cooling and pressurizing of electrical enclosures. Filter fans can be used as forced air cooling or in conjunction with an exhaust filter for convection cooling. They are designed to maintain a desired temperature within an enclosure.

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation



Product Details

General

| | |
|-------------|--|
| Application | <ul style="list-style-type: none"> • Ventilation • Temperature Control |
| Color | Black |
| Cutout | 8.81x8.81 |
| Material | ABS Plastic |
| Type | Filter Fan |
| UPC | 786725886807 |

Dimensions

| | |
|---------------|--------|
| Actual Depth | 4.9 in |
| Actual Height | 9.8 in |
| Actual Width | 9.8 in |
| Depth | 5 in |
| Height | 10 in |
| Width | 10 in |

Electrical Ratings

| | |
|----------------|---------|
| Voltage Rating | 115 VAC |
|----------------|---------|

Certifications and Compliance

| | |
|------------------|-------------------|
| Certified Listed | UL/cUL Recognized |
|------------------|-------------------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|