

## Compression Splice Conventional (Hex Die) Jumper Loop-Partial Tension

By FARGO  
Catalog # 40134



\*Representative Image

"Compression Splice, Conventional 2-Die, Jumper Loop, for AAC, AAAC, ACAR, ACSR, SAC Dia. Range: 0.806"-0.883", COMP/TW Dia. Range: 0.745"-0.825""

### General

Aluminum Die	34AH
Compression Method	Conventional
Inhibitor Loaded	No
Material	Aluminum Alloy
Press Minimum	60 to

### Dimensions

Length Before Compression	10 in
Messenger Diameter Range	0 - 0

### Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

### Conductor Related

Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	1.248 in
Conductor Diameter - Minimum	1.248 in
Conductor Diameter Range	1.248 - 1.248

### Certifications and Compliance

UL Listed	No
-----------	----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)