

Compression Deadend

By FARGO
Catalog # [861022](#)

Compression Deadend, Static Wire, No Jumper Pad, for EHS Steel, Alumoweld(R), Dia. Range 0.306 - 0.312



*Representative Image

Features

- Full Tension for Alumoweld conductor
- Body Forged Steel

General

| | |
|---------------------|----------------------------|
| Compression Method | Single Die |
| EU RoHS Indicator | No |
| Material | Steel |
| Material - Body | Galvanized Forged Steel |
| Material - Hardware | Aluminum Alloy |
| Material - Pad | Cast Aluminum |
| Press Minimum | 12 to |
| Product Category | Steel |
| Style | Static Wire, No Jumper Pad |
| Type | Compression |
| UPC | 096359251705 |

Dimensions

| | |
|------------------------------|----------|
| Diameter - Clamping Hardware | 0 in |
| Length Before Compression | 10.6 in |
| Messenger Diameter Range | 0 - 0 |
| Weight | 1.960 lb |

Conductor Related

| | |
|---------------------------------|---------------|
| Clamping Range | 0- 0 |
| Conductor Diameter (Main) Range | 0 - 0 |
| Conductor Diameter - Maximum | 0.312 in |
| Conductor Diameter - Minimum | 0.306 in |
| Conductor Diameter Range | 0.306 - 0.312 |

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)