

## Compression Deadend

By FARGO  
Catalog # [861227](#)

Compression Deadend, Static Wire, No Jumper Pad, for EHS Steel, Alumoweld(R), Dia. Range 0.385 - 0.392



\*Representative Image

### Features

- Full Tension for Alumoweld conductor
- Body Forged Steel

### General

Compression Method	Single Die
EU RoHS Indicator	No
Material	Steel
Material - Body	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pad	Cast Aluminum
Press Minimum	12 to
Product Category	Steel
Style	Static Wire, No Jumper Pad
Type	Compression
UPC	096359251729

### Dimensions

Diameter - Clamping Hardware	0 in
Length Before Compression	10.6 in
Messenger Diameter Range	0 - 0
Weight	1.840 lb

### Conductor Related

Clamping Range	0- 0
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	0.392 in
Conductor Diameter - Minimum	0.385 in
Conductor Diameter Range	0.385 - 0.392

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)