

Compression Deadend

By FARGO
Catalog # [861635S](#)

Compression Deadend, Static Wire, 2-hole Pad, for EHS Steel, Alumoweld(R), Dia. Range 0.486 - 0.495



Features

- Full Tension for Alumoweld conductor
- Body Forged Steel
- 2-hole pad cast aluminum NEMA hole spacing

General

Compression Method	Single Die
EU RoHS Indicator	No
Material	Steel
Material - Body	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pad	Cast Aluminum
Number of Bolt Holes	2
Press Minimum	60 to
Product Category	Steel
Style	Static Wire, 2-hole Pad
Type	Compression
UPC	096359270751

Dimensions

Diameter - Clamping Hardware	0 in
Length Before Compression	13.4 in
Messenger Diameter Range	0 - 0
Weight	3.500 lb

Conductor Related

Clamping Range	0- 0
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	0.495 in
Conductor Diameter - Minimum	0.486 in
Conductor Diameter Range	0.486 - 0.495

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)