

Compression Deadend

By FARGO
Catalog # [A011666NT](#)

Compression Deadend, Uni-Grip, Single Tongue, Vertical Eye, for ACSR 1510.5 kcmil 54/19, Without Terminal



*Representative Image

Features

- For use with ACSR code name Parrot
- Full tension Deadend assembly
- Steel eye factory compressed in Vertical orientation
- Prefilled with joint compound
- Uni-Grip Deadends & Jumper Terminals for conductors 1" dia or larger are EHV rated
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

General

Compression Method	Uni-Grip (single die system)
Die Size	16CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Number of Bolt Holes	4
Press Minimum	60 to
Product Category	Eye
Style	Uni-Grip, Single Tongue, Vertical Eye
Terminal Option	No
Type	Eye

Dimensions

Diameter - Clamping Hardware	0 in
Diameter - Outside	1.505 in
Length Before Compression	23.5 in
Messenger Diameter Range	0 - 0
Width - Pad	3 in

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Parrot-1510.5-54/19
Conductor Diameter (Main) Range	0 - 0

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)