

## Compression Deadend

By FARGO  
Catalog # [A011770](#)

Compression Deadend, Uni-Grip, Single Tongue, Vertical Eye,  
for ACSR 1869 kcmil 68/7, With Terminal



\*Representative Image

### Features

- For use with ACSR code name Seahawk
- Full tension Deadend assembly
- Steel eye factory compressed in Vertical orientation
- Prefilled with joint compound
- Uni-Grip Deadends & Jumper Terminals for conductors 1" dia or larger are EHV rated
- Jumper Terminal & Mounting Hardware included

### General

Compression Method	Uni-Grip (single die system)
Die Size	17CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	4
Press Minimum	60 to
Product Category	Eye
Style	Uni-Grip, Single Tongue, Vertical Eye
Type	Eye

### Dimensions

Diameter - Clamping Hardware	0 in
Diameter - Outside	1.603 in
Length Before Compression	24.4 in
Messenger Diameter Range	0 - 0
Width - Pad	4 in

### Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

### Conductor Related

Clamping Range	0 - 0
Conductor Diameter (Main) Range	0 - 0

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)