

## Compression Deadend

By FARGO  
Catalog # [A020709](#)

Compression Deadend, Uni-Grip, Double Tongue, Vertical Eye,  
for ACSR 266.8 kcmil 6/7, With Terminals



\*Representative Image

### General

Compression Method	Uni-Grip (single die system)
Die Size	07CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	2
Press Minimum	12 to
Product Category	Eye
Style	Uni-Grip, Single Tongue, Vertical Eye
Type	Eye

### Dimensions

Diameter - Clamping Hardware	0 in
Diameter - Outside	0.633 in
Length Before Compression	12.2 in
Messenger Diameter Range	0 - 0
Width - Pad	2 in

### Electrical Ratings

Voltage Application	Standard
---------------------	----------

### Conductor Related

Clamping Range	0 - 0
Conductor Diameter (Main) Range	0 - 0

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)