

Compression Deadend

By FARGO  
Catalog # [A021018NT](#)

Compression Deadend, Uni-Grip, Double Tongue, Vertical Eye,  
for ACSR 397.5 kcmil 30/7, Without Terminals



\*Representative Image

Features

- For use with ACSR code name Lark
- Full tension Deadend assembly
- Steel eye factory compressed in Vertical orientation
- Prefilled with joint compound
- Uni-Grip Deadends & Jumper Terminals for conductors 1" dia or larger are EHV rated
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

General

Compression Method	Uni-Grip (single die system)
Die Size	10CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Number of Bolt Holes	2
Press Minimum	60 to
Product Category	Eye
Style	Uni-Grip, Single Tongue, Vertical Eye
Terminal Option	No
Type	Compression
UPC	096359488521

Dimensions

Diameter - Clamping Hardware	0 in
Diameter - Outside	0.806 in
Length Before Compression	14.9 in
Messenger Diameter Range	0 - 0
Width - Pad	2 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Lark-397.5-30/7
Conductor Diameter (Main) Range	0 - 0

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)

