

## Compression Deadend

By FARGO  
Catalog # [A030813](#)

Compression Deadend, Uni-Grip, Single Tongue, Horizontal Eye, for ACSR 336.4 kcmil 26/7, With Terminal



\*Representative Image

### Features

- For use with ACSR code name Linnet
- Full tension Deadend assembly
- Steel eye factory compressed in Horizontal orientation
- Prefilled with joint compound
- Uni-Grip Deadends & Jumper Terminals for conductors 1" dia or larger are EHV rated
- Jumper Terminal & Mounting Hardware included

### General

Compression Method	Uni-Grip (single die system)
Die Size	O8CD
EU RoHS Indicator	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	2
Press Minimum	12 to
Product Category	Eye
Style	Uni-Grip, Single Tongue, Horizontal Eye
Type	Eye
UPC	096359276654

### Dimensions

Diameter - Clamping Hardware	0 in
Diameter - Outside	0.72 in
Length Before Compression	13.2 in
Messenger Diameter Range	0 - 0
Weight	2.040 lb
Width - Pad	2 in

### Electrical Ratings

Voltage Application	Standard
---------------------	----------

### Conductor Related

Clamping Range	0 - 0
Conductor Compatibility	ACSR-Linnet-336.4-26/7
Conductor Diameter (Main) Range	0 - 0

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)